

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1500433

Luminaire Tested: LD4C65D010 EU4659035 4LBMH

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-2019
Report Number: P1500433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659035 4LBMH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBM TRIM FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5087.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1500433

CATALOG NUMBER: LD4C65D010 EU4659035 4LBMH

Luminous Intensity Polar Plot



TEST NUMBER: P1500433

CATALOG NUMBER: LD4C65D010 EU4659035 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	619685
5°	610682
10°	585171
15°	552692
20°	515905
25°	468325
30°	391006
35°	283260
40°	177325
45°	101361
50°	52846
55°	29622
60°	18870
65°	11163
70°	8262
75°	3655
80°	5448
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 101361 cd/sqm

TEST NUMBER: P1500433

CATALOG NUMBER: LD4C65D010 EU4659035 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.1	9.1
10°-20°	1217.6	23.9
20°-30°	1564.9	30.8
30°-40°	1177.4	23.1
40°-50°	472.9	9.3
50°-60°	134.4	2.6
60°-70°	42.6	0.8
70°-80°	12.1	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3246.6	63.8
0°-40°	4424.0	87.0
0°-60°	5031.3	98.9
0°-90°	5087.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5087.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5044	
5°	4952	464
15°	4346	1218
25°	3455	1565
35°	1889	1177
45°	583	473
55°	138	134
65°	38	43
75°	8	12
85°	0	1
90°	0	

TEST NUMBER: P1500433

CATALOG NUMBER: LD4C65D010 EU4659035 4LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5044.1
2.5°	5013.4
5°	4951.9
7.5°	4836.7
10°	4690.8
12.5°	4514.5
15°	4345.5
17.5°	4153.5
20°	3946.1
22.5°	3723.7
25°	3454.9
27.5°	3132.3
30°	2756.3
32.5°	2333.9
35°	1888.7
37.5°	1474.0
40°	1105.7
42.5°	813.8
45°	583.4
47.5°	399.4
50°	276.5
52.5°	192.0
55°	138.3
57.5°	99.8
60°	76.8
62.5°	53.8
65°	38.4
67.5°	30.7
70°	23.0
72.5°	15.4
75°	7.7
77.5°	7.7
80°	7.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)