

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856997

Luminaire Tested: **LD4C15D010 EU4159050 4LBHYH**

Issue Date: 10/18/2023



Test Information

Test Method: LM-79-08
Report Number: P856997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)
Test Lab: INNOVATION CENTER
Issue Date: 10/18/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EU4159050 4LBHYH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LCHYP TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 971.6 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856997

CATALOG NUMBER: LD4C15D010 EU4159050 4LBHYH

Luminous Intensity Polar Plot





TEST NUMBER: P856997

CATALOG NUMBER: LD4C15D010 EU4159050 4LBHYH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	94	92		95	93	91		93
4	103	97	92	89	101	96	92	88	94	90	87		92	89	86		90
5	99	92	88	84	97	92	87	84	90	86	83		88	85	83		87
6	95	89	84	81	94	88	83	80	86	83	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	83	76	71	68	83	76	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	312490
5°	304225
10°	263956
15°	203665
20°	141903
25°	74785
30°	20910
35°	9269
40°	4619
45°	2398
50°	1032
55°	129
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856997

CATALOG NUMBER: LD4C15D010 EU4159050 4LBHYH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.8	23.0
10°-20°	437.8	45.1
20°-30°	253.0	26.0
30°-40°	44.4	4.6
40°-50°	11.3	1.2
50°-60°	1.2	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.6	94.1
0°-40°	959.0	98.7
0°-60°	971.6	100.0
0°-90°	971.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2544	
5°	2467	224
15°	1601	438
25°	552	253
35°	62	44
45°	14	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856997

CATALOG NUMBER: LD4C15D010 EU4159050 4LBHYH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2543.6
2.5°	2539.5
5°	2466.9
7.5°	2315.4
10°	2115.9
12.5°	1882.2
15°	1601.3
17.5°	1311.9
20°	1085.4
22.5°	815.4
25°	551.7
27.5°	315.8
30°	147.4
32.5°	100.6
35°	61.8
37.5°	41.4
40°	28.8
42.5°	19.8
45°	13.8
47.5°	9.0
50°	5.4
52.5°	2.4
55°	0.6
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)