

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857038

Luminaire Tested: **LX4C15D010 EX4C159830 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159830 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 860.5 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857038

CATALOG NUMBER: LX4C15D010 EX4C159830 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857038

CATALOG NUMBER: LX4C15D010 EX4C159830 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132731
5°	129773
10°	119996
15°	107664
20°	94785
25°	81563
30°	65695
35°	43733
40°	22757
45°	10303
50°	4472
55°	2999
60°	1917
65°	1366
70°	1114
75°	759
80°	0
85°	0



TEST NUMBER: P857038

CATALOG NUMBER: LX4C15D010 EX4C159830 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	11.3
10°-20°	236.4	27.5
20°-30°	274.5	31.9
30°-40°	181.8	21.1
40°-50°	51.0	5.9
50°-60°	12.8	1.5
60°-70°	4.8	0.6
70°-80°	1.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.4	70.7
0°-40°	790.3	91.8
0°-60°	854.1	99.2
0°-90°	860.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1080	
5°	1052	97
15°	846	236
25°	602	275
35°	292	182
45°	59	51
55°	14	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P857038

CATALOG NUMBER: LX4C15D010 EX4C159830 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1080.4
2.5°	1075.7
5°	1052.3
7.5°	1011.8
10°	961.9
12.5°	905.7
15°	846.5
17.5°	788.8
20°	725.0
22.5°	665.7
25°	601.7
27.5°	541.0
30°	463.1
32.5°	380.4
35°	291.6
37.5°	208.9
40°	141.9
42.5°	91.9
45°	59.3
47.5°	35.8
50°	23.4
52.5°	17.1
55°	14.0
57.5°	11.0
60°	7.8
62.5°	6.2
65°	4.7
67.5°	3.1
70°	3.1
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)