

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857049

Luminaire Tested: **LX4C15D010 EX4C159835 4LBMH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857049  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C15D010 EX4C159835 4LBMH  
Description:  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1050.5 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857049

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P857049

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 97  | 96  | 96  | 94  | 93  | 91  |    |    |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 95  | 91  | 88  | 91  | 88  | 86  | 89  | 86  | 84  | 82  |    |    |
| 3   | 99  | 91  | 85  | 80  | 97  | 90  | 84  | 80  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  |    |    |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 64  | 74  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 62  | 61  |    |    |
| 6   | 81  | 71  | 64  | 58  | 80  | 70  | 63  | 58  | 68  | 62  | 58  | 67  | 61  | 57  | 65  | 61  | 57  | 55  |    |    |
| 7   | 76  | 65  | 58  | 53  | 75  | 65  | 58  | 53  | 63  | 57  | 53  | 62  | 56  | 52  | 61  | 56  | 52  | 50  |    |    |
| 8   | 72  | 60  | 53  | 49  | 70  | 60  | 53  | 49  | 59  | 53  | 48  | 58  | 52  | 48  | 57  | 52  | 48  | 46  |    |    |
| 9   | 68  | 56  | 49  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 44  | 43  |    |    |
| 10  | 64  | 52  | 46  | 41  | 63  | 52  | 46  | 41  | 51  | 45  | 41  | 50  | 45  | 41  | 49  | 44  | 41  | 39  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 83184 |
| 5°  | 83502 |
| 10° | 83756 |
| 15° | 83766 |
| 20° | 83293 |
| 25° | 81346 |
| 30° | 76022 |
| 35° | 65840 |
| 40° | 51432 |
| 45° | 36903 |
| 50° | 23986 |
| 55° | 14351 |
| 60° | 8403  |
| 65° | 5378  |
| 70° | 3592  |
| 75° | 2706  |
| 80° | 2052  |
| 85° | 0     |



TEST NUMBER: P857049

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 64.5   | 6.1       |
| 10°-20°   | 185.8  | 17.7      |
| 20°-30°   | 274.2  | 26.1      |
| 30°-40°   | 270.6  | 25.8      |
| 40°-50°   | 165.6  | 15.8      |
| 50°-60°   | 63.5   | 6.0       |
| 60°-70°   | 19.9   | 1.9       |
| 70°-80°   | 5.8    | 0.6       |
| 80°-90°   | 0.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 524.4  | 49.9      |
| 0°-40°    | 795.0  | 75.7      |
| 0°-60°    | 1024.0 | 97.5      |
| 0°-90°    | 1050.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1050.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 677 |      |
| 5°  | 677 | 64   |
| 15° | 659 | 186  |
| 25° | 600 | 274  |
| 35° | 439 | 271  |
| 45° | 212 | 166  |
| 55° | 67  | 63   |
| 65° | 18  | 20   |
| 75° | 6   | 6    |
| 85° | 0   | 1    |
| 90° | 0   |      |



TEST NUMBER: P857049

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBMH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 677.1 |
| 2.5°  | 678.5 |
| 5°    | 677.1 |
| 7.5°  | 675.7 |
| 10°   | 671.4 |
| 12.5° | 665.7 |
| 15°   | 658.6 |
| 17.5° | 650.0 |
| 20°   | 637.1 |
| 22.5° | 623.0 |
| 25°   | 600.1 |
| 27.5° | 571.6 |
| 30°   | 535.9 |
| 32.5° | 491.8 |
| 35°   | 439.0 |
| 37.5° | 380.6 |
| 40°   | 320.7 |
| 42.5° | 265.1 |
| 45°   | 212.4 |
| 47.5° | 165.3 |
| 50°   | 125.5 |
| 52.5° | 92.7  |
| 55°   | 67.0  |
| 57.5° | 47.0  |
| 60°   | 34.2  |
| 62.5° | 25.7  |
| 65°   | 18.5  |
| 67.5° | 14.3  |
| 70°   | 10.0  |
| 72.5° | 7.1   |
| 75°   | 5.7   |
| 77.5° | 2.9   |
| 80°   | 2.9   |
| 82.5° | 1.4   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)