

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856930

Luminaire Tested: **LX4C15D010 EU4159030 4LBHYLI**

Issue Date: 7/20/2023



Test Information

Test Method: LM-79-08
Report Number: P856930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EU4159030 4LBHYLI
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1219.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856930

CATALOG NUMBER: LX4C15D010 EU4159030 4LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P856930

CATALOG NUMBER: LX4C15D010 EU4159030 4LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78
10	85	78	74	71	84	78	73	71	77	73	70		76	73	70		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	463268
5°	451571
10°	382854
15°	248142
20°	154101
25°	82945
30°	28514
35°	11488
40°	3063
45°	1373
50°	535
55°	236
60°	147
65°	174
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856930

CATALOG NUMBER: LX4C15D010 EU4159030 4LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.3	27.1
10°-20°	544.7	44.7
20°-30°	282.4	23.2
30°-40°	53.5	4.4
40°-50°	6.8	0.6
50°-60°	1.0	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.4	94.9
0°-40°	1210.9	99.3
0°-60°	1218.7	100.0
0°-90°	1219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1219.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3771	
5°	3662	330
15°	1951	545
25°	612	282
35°	77	53
45°	8	7
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856930

CATALOG NUMBER: LX4C15D010 EU4159030 4LBHYLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3770.9
2.5°	3764.7
5°	3661.7
7.5°	3425.3
10°	3069.0
12.5°	2532.5
15°	1951.0
17.5°	1481.6
20°	1178.7
22.5°	878.7
25°	611.9
27.5°	376.0
30°	201.0
32.5°	135.7
35°	76.6
37.5°	33.2
40°	19.1
42.5°	12.4
45°	7.9
47.5°	4.5
50°	2.8
52.5°	1.1
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)