

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857062

Luminaire Tested: **LX4C15D010 EX4C159840 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159840 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1051.4 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857062

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857062

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83246
5°	83563
10°	83819
15°	83829
20°	83372
25°	81414
30°	76093
35°	65900
40°	51480
45°	36937
50°	24005
55°	14372
60°	8403
65°	5378
70°	3592
75°	2706
80°	2052
85°	0



TEST NUMBER: P857062

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	6.1
10°-20°	185.9	17.7
20°-30°	274.4	26.1
30°-40°	270.8	25.8
40°-50°	165.7	15.8
50°-60°	63.5	6.0
60°-70°	19.9	1.9
70°-80°	5.8	0.6
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.9	49.9
0°-40°	795.7	75.7
0°-60°	1024.9	97.5
0°-90°	1051.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1051.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	678	
5°	678	65
15°	659	186
25°	601	274
35°	439	271
45°	213	166
55°	67	64
65°	18	20
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P857062

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	677.6
2.5°	679.1
5°	677.6
7.5°	676.2
10°	671.9
12.5°	666.2
15°	659.1
17.5°	650.5
20°	637.7
22.5°	623.5
25°	600.6
27.5°	572.1
30°	536.4
32.5°	492.2
35°	439.4
37.5°	380.9
40°	321.0
42.5°	265.4
45°	212.6
47.5°	165.4
50°	125.6
52.5°	92.7
55°	67.1
57.5°	47.1
60°	34.2
62.5°	25.7
65°	18.5
67.5°	14.3
70°	10.0
72.5°	7.1
75°	5.7
77.5°	2.9
80°	2.9
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)