

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857064

Luminaire Tested: **LX4C15D010 EX4C159840 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857064
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159840 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 873.9 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857064

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857064

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134795
5°	131807
10°	121855
15°	109343
20°	96249
25°	82837
30°	66702
35°	44408
40°	23094
45°	10459
50°	4530
55°	3041
60°	1941
65°	1366
70°	1149
75°	759
80°	0
85°	0



TEST NUMBER: P857064

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	11.3
10°-20°	240.1	27.5
20°-30°	278.8	31.9
30°-40°	184.6	21.1
40°-50°	51.8	5.9
50°-60°	13.0	1.5
60°-70°	4.9	0.6
70°-80°	1.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.9	70.7
0°-40°	802.5	91.8
0°-60°	867.3	99.3
0°-90°	873.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1097	
5°	1069	99
15°	860	240
25°	611	279
35°	296	185
45°	60	52
55°	14	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P857064

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1097.2
2.5°	1092.5
5°	1068.8
7.5°	1027.6
10°	976.8
12.5°	919.8
15°	859.7
17.5°	801.1
20°	736.2
22.5°	676.0
25°	611.1
27.5°	549.4
30°	470.2
32.5°	386.3
35°	296.1
37.5°	212.1
40°	144.0
42.5°	93.4
45°	60.2
47.5°	36.5
50°	23.7
52.5°	17.4
55°	14.2
57.5°	11.1
60°	7.9
62.5°	6.3
65°	4.7
67.5°	3.2
70°	3.2
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)