

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856962

Luminaire Tested: **LX4C15D010 EX4C159035 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P856962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159035 4LBSH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1538.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856962

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P856962

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98823
5°	98362
10°	96331
15°	92834
20°	88562
25°	83786
30°	79030
35°	74418
40°	70067
45°	65309
50°	59555
55°	52605
60°	44522
65°	34942
70°	24928
75°	13670
80°	2405
85°	0



TEST NUMBER: P856962

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.3	4.9
10°-20°	204.8	13.3
20°-30°	284.4	18.5
30°-40°	310.3	20.2
40°-50°	289.5	18.8
50°-60°	219.8	14.3
60°-70°	120.3	7.8
70°-80°	33.1	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	564.5	36.7
0°-40°	874.9	56.9
0°-60°	1384.1	90.0
0°-90°	1538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	804	
5°	798	75
15°	730	205
25°	618	284
35°	496	310
45°	376	289
55°	246	220
65°	120	120
75°	29	33
85°	0	0
90°	0	



TEST NUMBER: P856962

CATALOG NUMBER: LX4C15D010 EX4C159035 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	804.4
2.5°	804.4
5°	797.6
7.5°	787.5
10°	772.2
12.5°	751.9
15°	729.9
17.5°	702.8
20°	677.4
22.5°	646.9
25°	618.1
27.5°	589.3
30°	557.1
32.5°	526.6
35°	496.2
37.5°	465.7
40°	436.9
42.5°	406.4
45°	375.9
47.5°	345.4
50°	311.6
52.5°	279.4
55°	245.6
57.5°	213.4
60°	181.2
62.5°	149.0
65°	120.2
67.5°	93.1
70°	69.4
72.5°	47.4
75°	28.8
77.5°	13.5
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)