

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856974

Luminaire Tested: **LD4C15D010 EU4159040 4LBHYH**

Issue Date: 10/18/2023



Test Information

Test Method: LM-79-08
Report Number: P856974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)
Test Lab: INNOVATION CENTER
Issue Date: 10/18/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EU4159040 4LBHYH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LCHYP TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 952.3 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856974

CATALOG NUMBER: LD4C15D010 EU4159040 4LBHYH

Luminous Intensity Polar Plot





TEST NUMBER: P856974

CATALOG NUMBER: LD4C15D010 EU4159040 4LBHYH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	94	92		95	93	91		93
4	103	97	92	89	101	96	92	88	94	90	87		92	89	86		90
5	99	92	88	84	97	92	87	84	90	86	83		88	85	83		87
6	95	89	84	81	94	88	83	80	86	83	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	83	76	71	68	83	76	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306323
5°	298219
10°	258741
15°	199646
20°	139118
25°	73321
30°	20499
35°	9074
40°	4523
45°	2346
50°	1013
55°	129
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P856974

CATALOG NUMBER: LD4C15D010 EU4159040 4LBHYH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.4	23.0
10°-20°	429.1	45.1
20°-30°	248.0	26.0
30°-40°	43.5	4.6
40°-50°	11.1	1.2
50°-60°	1.2	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	896.6	94.1
0°-40°	940.1	98.7
0°-60°	952.3	100.0
0°-90°	952.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	952.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2493	
5°	2418	219
15°	1570	429
25°	541	248
35°	60	43
45°	14	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P856974

CATALOG NUMBER: LD4C15D010 EU4159040 4LBHYH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2493.4
2.5°	2489.3
5°	2418.2
7.5°	2269.6
10°	2074.1
12.5°	1845.0
15°	1569.7
17.5°	1286.0
20°	1064.1
22.5°	799.2
25°	540.9
27.5°	309.5
30°	144.5
32.5°	98.7
35°	60.5
37.5°	40.5
40°	28.2
42.5°	19.4
45°	13.5
47.5°	8.8
50°	5.3
52.5°	2.3
55°	0.6
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)