

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857104

Luminaire Tested: **LX4C15D010 EX4C159030 4LBNLI**

Issue Date: 1/21/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857104  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C15D010 EX4C159030 4LBNLI  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBN TRIM WITH LI FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1341.7 lumens  
Efficiency: N/A  
Efficacy: 57.3 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857104

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P857104

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 109 | 105 | 102 | 99  | 107 | 103 | 100 | 98  | 100 | 98  | 95  |  | 97  | 95  | 93  |  | 95  |
| 3   | 105 | 99  | 95  | 92  | 103 | 98  | 94  | 91  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 4   | 101 | 94  | 89  | 86  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 84  | 80  | 87  | 82  | 79  |  | 85  | 81  | 79  |  | 83  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 78  | 75  |  | 80  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  |
| 8   | 85  | 77  | 72  | 68  | 84  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  |
| 9   | 82  | 74  | 69  | 65  | 81  | 73  | 68  | 65  | 72  | 68  | 65  |  | 72  | 68  | 65  |  | 71  |
| 10  | 79  | 71  | 66  | 62  | 78  | 70  | 65  | 62  | 69  | 65  | 62  |  | 69  | 65  | 62  |  | 68  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 424164 |
| 5°  | 381696 |
| 10° | 295891 |
| 15° | 214171 |
| 20° | 148296 |
| 25° | 108104 |
| 30° | 78561  |
| 35° | 46478  |
| 40° | 19550  |
| 45° | 6098   |
| 50° | 803    |
| 55° | 450    |
| 60° | 516    |
| 65° | 610    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P857104

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 272.1  | 20.3      |
| 10°-20°   | 465.8  | 34.7      |
| 20°-30°   | 370.2  | 27.6      |
| 30°-40°   | 196.0  | 14.6      |
| 40°-50°   | 33.8   | 2.5       |
| 50°-60°   | 2.6    | 0.2       |
| 60°-70°   | 1.3    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1108.1 | 82.6      |
| 0°-40°    | 1304.0 | 97.2      |
| 0°-60°    | 1340.4 | 99.9      |
| 0°-90°    | 1341.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1341.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3453 |      |
| 5°  | 3095 | 272  |
| 15° | 1684 | 466  |
| 25° | 798  | 370  |
| 35° | 310  | 196  |
| 45° | 35   | 34   |
| 55° | 2    | 3    |
| 65° | 2    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P857104

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNLI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3452.6 |
| 2.5°  | 3363.7 |
| 5°    | 3095.1 |
| 7.5°  | 2743.9 |
| 10°   | 2371.9 |
| 12.5° | 2012.4 |
| 15°   | 1683.9 |
| 17.5° | 1378.1 |
| 20°   | 1134.3 |
| 22.5° | 948.3  |
| 25°   | 797.5  |
| 27.5° | 675.6  |
| 30°   | 553.8  |
| 32.5° | 429.8  |
| 35°   | 309.9  |
| 37.5° | 204.6  |
| 40°   | 121.9  |
| 42.5° | 70.2   |
| 45°   | 35.1   |
| 47.5° | 12.4   |
| 50°   | 4.2    |
| 52.5° | 4.2    |
| 55°   | 2.1    |
| 57.5° | 2.1    |
| 60°   | 2.1    |
| 62.5° | 2.1    |
| 65°   | 2.1    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)