

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856979

Luminaire Tested: **LX4C15D010 EX4C159040 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P856979
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159040 4LBMDH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1115.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856979

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P856979

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81
4	97	90	84	80	95	88	83	79	86	82	78	84	80	77	82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	63	60	68	63	59	67	62	59	66	62	59	57
9	76	66	60	56	74	65	60	56	64	59	56	64	59	56	63	58	55	54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165029
5°	162798
10°	155162
15°	143569
20°	129248
25°	107372
30°	78051
35°	50602
40°	30615
45°	15776
50°	7148
55°	4305
60°	2875
65°	2064
70°	1545
75°	1044
80°	637
85°	423



TEST NUMBER: P856979

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.6	11.1
10°-20°	315.0	28.3
20°-30°	356.2	31.9
30°-40°	215.3	19.3
40°-50°	75.4	6.8
50°-60°	19.3	1.7
60°-70°	7.4	0.7
70°-80°	2.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.8	71.3
0°-40°	1010.1	90.6
0°-60°	1104.8	99.1
0°-90°	1115.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1115.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1343	
5°	1320	124
15°	1129	315
25°	792	356
35°	337	215
45°	91	75
55°	20	19
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P856979

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1343.3
2.5°	1337.7
5°	1320.1
7.5°	1288.9
10°	1243.8
12.5°	1189.4
15°	1128.8
17.5°	1062.4
20°	988.6
22.5°	898.1
25°	792.1
27.5°	670.7
30°	550.2
32.5°	435.0
35°	337.4
37.5°	255.8
40°	190.9
42.5°	137.2
45°	90.8
47.5°	55.9
50°	37.4
52.5°	26.9
55°	20.1
57.5°	15.4
60°	11.7
62.5°	9.3
65°	7.1
67.5°	5.6
70°	4.3
72.5°	3.1
75°	2.2
77.5°	1.5
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)