

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856988

Luminaire Tested: **LX4C15D010 EX4C159040 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P856988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159040 4LBWH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1311.1 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856988

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P856988

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	67	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103811
5°	104208
10°	104527
15°	104535
20°	103963
25°	101516
30°	94889
35°	82172
40°	64198
45°	46059
50°	29911
55°	17906
60°	10492
65°	6715
70°	4490
75°	3370
80°	2547
85°	0



TEST NUMBER: P856988

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.5	6.1
10°-20°	231.9	17.7
20°-30°	342.1	26.1
30°-40°	337.7	25.8
40°-50°	206.6	15.8
50°-60°	79.2	6.0
60°-70°	24.8	1.9
70°-80°	7.3	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.5	49.9
0°-40°	992.2	75.7
0°-60°	1278.0	97.5
0°-90°	1311.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1311.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	845	
5°	845	80
15°	822	232
25°	749	342
35°	548	338
45°	265	207
55°	84	79
65°	23	25
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P856988

CATALOG NUMBER: LX4C15D010 EX4C159040 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	845.0
2.5°	846.8
5°	845.0
7.5°	843.2
10°	837.9
12.5°	830.8
15°	821.9
17.5°	811.2
20°	795.2
22.5°	777.4
25°	748.9
27.5°	713.3
30°	668.9
32.5°	613.8
35°	547.9
37.5°	475.0
40°	400.3
42.5°	330.9
45°	265.1
47.5°	206.3
50°	156.5
52.5°	115.7
55°	83.6
57.5°	58.7
60°	42.7
62.5°	32.1
65°	23.1
67.5°	17.8
70°	12.5
72.5°	8.9
75°	7.1
77.5°	3.6
80°	3.6
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)