

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857534

Luminaire Tested: **LX4C30D010 EX4C309030 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309030 4LBMDH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2089.0 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857534

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857534

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309173
5°	305002
10°	290702
15°	268988
20°	242153
25°	201175
30°	146228
35°	94800
40°	57366
45°	29571
50°	13379
55°	8053
60°	5406
65°	3866
70°	2910
75°	1946
80°	1203
85°	846



TEST NUMBER: P857534

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.5	11.1
10°-20°	590.2	28.3
20°-30°	667.4	31.9
30°-40°	403.3	19.3
40°-50°	141.3	6.8
50°-60°	36.1	1.7
60°-70°	13.8	0.7
70°-80°	4.7	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1489.1	71.3
0°-40°	1892.4	90.6
0°-60°	2069.8	99.1
0°-90°	2089.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2089.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2517	
5°	2473	232
15°	2115	590
25°	1484	667
35°	632	403
45°	170	141
55°	38	36
65°	13	14
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P857534

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2516.6
2.5°	2506.2
5°	2473.2
7.5°	2414.8
10°	2330.3
12.5°	2228.4
15°	2114.9
17.5°	1990.5
20°	1852.2
22.5°	1682.6
25°	1484.1
27.5°	1256.6
30°	1030.8
32.5°	815.0
35°	632.1
37.5°	479.2
40°	357.7
42.5°	257.0
45°	170.2
47.5°	104.8
50°	70.0
52.5°	50.4
55°	37.6
57.5°	28.9
60°	22.0
62.5°	17.4
65°	13.3
67.5°	10.4
70°	8.1
72.5°	5.8
75°	4.1
77.5°	2.9
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)