

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857543

Luminaire Tested: **LX4C30D010 EX4C309030 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309030 4LBWH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2456.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857543

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857543

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194477
5°	195220
10°	195818
15°	195830
20°	194747
25°	190196
30°	177763
35°	153936
40°	120248
45°	86280
50°	56057
55°	33542
60°	19632
65°	12616
70°	8405
75°	6313
80°	4740
85°	0



TEST NUMBER: P857543

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	6.1
10°-20°	434.4	17.7
20°-30°	641.0	26.1
30°-40°	632.6	25.8
40°-50°	387.1	15.8
50°-60°	148.4	6.0
60°-70°	46.4	1.9
70°-80°	13.6	0.6
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1226.1	49.9
0°-40°	1858.7	75.7
0°-60°	2394.2	97.5
0°-90°	2456.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2456.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1583	
5°	1583	151
15°	1540	434
25°	1403	641
35°	1026	633
45°	497	387
55°	157	148
65°	43	46
75°	13	14
85°	0	2
90°	0	



TEST NUMBER: P857543

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1583.0
2.5°	1586.4
5°	1583.0
7.5°	1579.7
10°	1569.7
12.5°	1556.4
15°	1539.7
17.5°	1519.7
20°	1489.6
22.5°	1456.4
25°	1403.1
27.5°	1336.3
30°	1253.1
32.5°	1149.8
35°	1026.4
37.5°	889.8
40°	749.8
42.5°	619.9
45°	496.6
47.5°	386.5
50°	293.3
52.5°	216.7
55°	156.6
57.5°	109.9
60°	79.9
62.5°	60.0
65°	43.4
67.5°	33.4
70°	23.4
72.5°	16.7
75°	13.3
77.5°	6.7
80°	6.7
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)