

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857022

Luminaire Tested: **LX4C15D010 EX4C159827 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159827 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1094.2 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857022

CATALOG NUMBER: LX4C15D010 EX4C159827 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P857022

CATALOG NUMBER: LX4C15D010 EX4C159827 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		66
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176553
5°	182567
10°	184416
15°	166119
20°	138059
25°	108307
30°	79271
35°	40959
40°	19453
45°	6845
50°	1548
55°	1007
60°	713
65°	523
70°	395
75°	237
80°	212
85°	0



TEST NUMBER: P857022

CATALOG NUMBER: LX4C15D010 EX4C159827 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.4	12.9
10°-20°	359.8	32.9
20°-30°	364.0	33.3
30°-40°	185.6	17.0
40°-50°	36.4	3.3
50°-60°	4.4	0.4
60°-70°	1.8	0.2
70°-80°	0.7	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	865.2	79.1
0°-40°	1050.8	96.0
0°-60°	1091.6	99.8
0°-90°	1094.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1094.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1437	
5°	1480	141
15°	1306	360
25°	799	364
35°	273	186
45°	39	36
55°	5	4
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P857022

CATALOG NUMBER: LX4C15D010 EX4C159827 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1437.1
2.5°	1450.4
5°	1480.4
7.5°	1497.6
10°	1478.3
12.5°	1413.4
15°	1306.1
17.5°	1179.6
20°	1056.0
22.5°	927.9
25°	799.0
27.5°	670.7
30°	558.8
32.5°	421.1
35°	273.1
37.5°	182.9
40°	121.3
42.5°	76.2
45°	39.4
47.5°	14.1
50°	8.1
52.5°	6.0
55°	4.7
57.5°	3.7
60°	2.9
62.5°	2.3
65°	1.8
67.5°	1.3
70°	1.1
72.5°	0.8
75°	0.5
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)