

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857056

Luminaire Tested: **LX4C15D010 EX4C159835 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159835 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1167.3 lumens
Efficiency: N/A
Efficacy: 73.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857056

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857056

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92435
5°	92788
10°	93063
15°	93076
20°	92562
25°	90387
30°	84491
35°	73158
40°	57141
45°	41003
50°	26643
55°	15957
60°	9337
65°	5988
70°	3987
75°	2990
80°	2264
85°	0



TEST NUMBER: P857056

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	6.1
10°-20°	206.4	17.7
20°-30°	304.6	26.1
30°-40°	300.6	25.8
40°-50°	184.0	15.8
50°-60°	70.6	6.0
60°-70°	22.1	1.9
70°-80°	6.5	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.7	49.9
0°-40°	883.4	75.7
0°-60°	1137.9	97.5
0°-90°	1167.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1167.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	752	
5°	752	72
15°	732	206
25°	667	305
35°	488	301
45°	236	184
55°	74	71
65°	21	22
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P857056

CATALOG NUMBER: LX4C15D010 EX4C159835 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	752.4
2.5°	754.0
5°	752.4
7.5°	750.8
10°	746.0
12.5°	739.7
15°	731.8
17.5°	722.2
20°	708.0
22.5°	692.2
25°	666.8
27.5°	635.1
30°	595.6
32.5°	546.5
35°	487.8
37.5°	422.9
40°	356.3
42.5°	294.6
45°	236.0
47.5°	183.7
50°	139.4
52.5°	103.0
55°	74.5
57.5°	52.3
60°	38.0
62.5°	28.5
65°	20.6
67.5°	15.9
70°	11.1
72.5°	7.9
75°	6.3
77.5°	3.2
80°	3.2
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)