

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857063

Luminaire Tested: **LX4C15D010 EX4C159840 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P857063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159840 4LBMLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1311.8 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857063

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857063

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	414716
5°	373199
10°	289317
15°	209401
20°	145001
25°	105705
30°	76802
35°	45443
40°	19117
45°	5959
50°	765
55°	450
60°	516
65°	610
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857063

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.0	20.3
10°-20°	455.4	34.7
20°-30°	362.0	27.6
30°-40°	191.6	14.6
40°-50°	33.0	2.5
50°-60°	2.5	0.2
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1083.4	82.6
0°-40°	1275.0	97.2
0°-60°	1310.5	99.9
0°-90°	1311.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1311.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3376	
5°	3026	266
15°	1646	455
25°	780	362
35°	303	192
45°	34	33
55°	2	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857063

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3375.7
2.5°	3288.7
5°	3026.2
7.5°	2682.8
10°	2319.2
12.5°	1967.6
15°	1646.4
17.5°	1347.4
20°	1109.1
22.5°	927.2
25°	779.8
27.5°	660.6
30°	541.4
32.5°	420.2
35°	303.0
37.5°	200.0
40°	119.2
42.5°	68.7
45°	34.3
47.5°	12.1
50°	4.0
52.5°	4.0
55°	2.1
57.5°	2.1
60°	2.1
62.5°	2.1
65°	2.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)