

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857576

Luminaire Tested: **LX4C30D010 EX4C309040 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309040 4LBMDH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2121.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857576

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857576

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313915
5°	309676
10°	295155
15°	273109
20°	245853
25°	204252
30°	148470
35°	96240
40°	58248
45°	30022
50°	13589
55°	8182
60°	5479
65°	3924
70°	2945
75°	1946
80°	1273
85°	846



TEST NUMBER: P857576

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.1	11.1
10°-20°	599.2	28.3
20°-30°	677.6	31.9
30°-40°	409.5	19.3
40°-50°	143.4	6.8
50°-60°	36.7	1.7
60°-70°	14.0	0.7
70°-80°	4.7	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1511.9	71.3
0°-40°	1921.4	90.6
0°-60°	2101.5	99.1
0°-90°	2121.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2121.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2555	
5°	2511	235
15°	2147	599
25°	1507	678
35°	642	409
45°	173	143
55°	38	37
65°	14	14
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P857576

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2555.2
2.5°	2544.6
5°	2511.1
7.5°	2451.8
10°	2366.0
12.5°	2262.5
15°	2147.3
17.5°	2021.0
20°	1880.5
22.5°	1708.4
25°	1506.8
27.5°	1275.8
30°	1046.6
32.5°	827.4
35°	641.7
37.5°	486.6
40°	363.2
42.5°	260.9
45°	172.8
47.5°	106.4
50°	71.1
52.5°	51.1
55°	38.2
57.5°	29.4
60°	22.3
62.5°	17.6
65°	13.5
67.5°	10.6
70°	8.2
72.5°	5.9
75°	4.1
77.5°	2.9
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)