

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857069

Luminaire Tested: **LX4C15D010 EX4C159840 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159840 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1169.1 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857069

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857069

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92570
5°	92924
10°	93212
15°	93216
20°	92706
25°	90523
30°	84619
35°	73278
40°	57253
45°	41072
50°	26681
55°	15957
60°	9361
65°	5988
70°	3987
75°	2990
80°	2264
85°	0



TEST NUMBER: P857069

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	6.1
10°-20°	206.8	17.7
20°-30°	305.1	26.1
30°-40°	301.1	25.8
40°-50°	184.3	15.8
50°-60°	70.6	6.0
60°-70°	22.1	1.9
70°-80°	6.5	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	583.6	49.9
0°-40°	884.8	75.7
0°-60°	1139.7	97.5
0°-90°	1169.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1169.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	754	
5°	754	72
15°	733	207
25°	668	305
35°	489	301
45°	236	184
55°	74	71
65°	21	22
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P857069

CATALOG NUMBER: LX4C15D010 EX4C159840 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	753.5
2.5°	755.1
5°	753.5
7.5°	751.9
10°	747.2
12.5°	740.9
15°	732.9
17.5°	723.4
20°	709.1
22.5°	693.2
25°	667.8
27.5°	636.1
30°	596.5
32.5°	547.4
35°	488.6
37.5°	423.6
40°	357.0
42.5°	295.1
45°	236.4
47.5°	184.0
50°	139.6
52.5°	103.2
55°	74.5
57.5°	52.3
60°	38.1
62.5°	28.6
65°	20.6
67.5°	15.9
70°	11.1
72.5°	7.9
75°	6.3
77.5°	3.2
80°	3.2
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)