

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857102

Luminaire Tested: **LX4C15D010 EX4C159030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P857102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159030 4LBMLI
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1709.8 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857102

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857102

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	540543
5°	486422
10°	377090
15°	272944
20°	188982
25°	137777
30°	100110
35°	59241
40°	24922
45°	7784
50°	1013
55°	557
60°	639
65°	756
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857102

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.7	20.3
10°-20°	593.6	34.7
20°-30°	471.8	27.6
30°-40°	249.8	14.6
40°-50°	43.0	2.5
50°-60°	3.2	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.1	82.6
0°-40°	1661.9	97.2
0°-60°	1708.2	99.9
0°-90°	1709.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1709.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4400	
5°	3944	347
15°	2146	594
25°	1016	472
35°	395	250
45°	45	43
55°	3	3
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857102

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4399.9
2.5°	4286.7
5°	3944.3
7.5°	3496.8
10°	3022.8
12.5°	2564.7
15°	2146.0
17.5°	1756.2
20°	1445.5
22.5°	1208.5
25°	1016.4
27.5°	861.1
30°	705.7
32.5°	547.8
35°	395.0
37.5°	260.8
40°	155.4
42.5°	89.5
45°	44.8
47.5°	15.8
50°	5.3
52.5°	5.3
55°	2.6
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)