

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857103

Luminaire Tested: **LX4C15D010 EX4C159030 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159030 4LBNH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1138.7 lumens
Efficiency: N/A
Efficacy: 48.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857103

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857103

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	76	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	175644
5°	171715
10°	158780
15°	142462
20°	125417
25°	107942
30°	86931
35°	57861
40°	30118
45°	13621
50°	5906
55°	3962
60°	2555
65°	1802
70°	1509
75°	997
80°	0
85°	0



TEST NUMBER: P857103

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	11.3
10°-20°	312.9	27.5
20°-30°	363.3	31.9
30°-40°	240.6	21.1
40°-50°	67.5	5.9
50°-60°	17.0	1.5
60°-70°	6.4	0.6
70°-80°	2.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	805.1	70.7
0°-40°	1045.7	91.8
0°-60°	1130.1	99.2
0°-90°	1138.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1138.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1430	
5°	1392	129
15°	1120	313
25°	796	363
35°	386	241
45°	78	67
55°	18	17
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P857103

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1429.7
2.5°	1423.4
5°	1392.4
7.5°	1338.7
10°	1272.8
12.5°	1198.5
15°	1120.1
17.5°	1043.7
20°	959.3
22.5°	880.8
25°	796.3
27.5°	715.9
30°	612.8
32.5°	503.4
35°	385.8
37.5°	276.5
40°	187.8
42.5°	121.7
45°	78.4
47.5°	47.4
50°	30.9
52.5°	22.7
55°	18.5
57.5°	14.5
60°	10.4
62.5°	8.2
65°	6.2
67.5°	4.2
70°	4.2
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)