

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857603

Luminaire Tested: **LX4C30D010 EX4C309050 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P857603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309050 4LBSH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2991.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857603

CATALOG NUMBER: LX4C30D010 EX4C309050 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P857603

CATALOG NUMBER: LX4C30D010 EX4C309050 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	108	105	102	99		101	98	96			97	95	93			93
2	102	96	90	85	100	94	88	84		90	86	82			87	83	80			84
3	95	85	78	73	92	84	77	72		81	75	71			78	74	70			76
4	87	77	69	63	85	75	68	63		73	67	62			71	65	61			69
5	81	69	61	55	79	68	61	55		66	60	55			64	59	54			63
6	75	63	55	49	73	62	54	49		60	54	49			59	53	48			57
7	70	58	50	44	68	57	49	44		55	49	44			54	48	43			53
8	65	53	45	40	64	52	45	40		51	44	39			50	44	39			49
9	61	49	41	36	60	48	41	36		47	40	36			46	40	36			45
10	58	45	38	33	56	45	38	33		44	37	33			43	37	33			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192180
5°	191286
10°	187335
15°	180530
20°	172221
25°	162936
30°	153704
35°	144712
40°	136254
45°	127022
50°	115822
55°	102275
60°	86587
65°	67965
70°	48528
75°	26581
80°	4669
85°	0



TEST NUMBER: P857603

CATALOG NUMBER: LX4C30D010 EX4C309050 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.5	4.9
10°-20°	398.3	13.3
20°-30°	553.1	18.5
30°-40°	603.5	20.2
40°-50°	563.0	18.8
50°-60°	427.3	14.3
60°-70°	234.0	7.8
70°-80°	64.4	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.9	36.7
0°-40°	1701.4	56.9
0°-60°	2691.7	90.0
0°-90°	2991.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2991.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1564	
5°	1551	147
15°	1419	398
25°	1202	553
35°	965	604
45°	731	563
55°	478	427
65°	234	234
75°	56	64
85°	0	1
90°	0	



TEST NUMBER: P857603

CATALOG NUMBER: LX4C30D010 EX4C309050 4LBSH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1564.3
2.5°	1564.3
5°	1551.1
7.5°	1531.4
10°	1501.7
12.5°	1462.2
15°	1419.4
17.5°	1366.7
20°	1317.3
22.5°	1258.0
25°	1202.0
27.5°	1146.1
30°	1083.5
32.5°	1024.2
35°	964.9
37.5°	905.6
40°	849.6
42.5°	790.4
45°	731.1
47.5°	671.8
50°	606.0
52.5°	543.4
55°	477.5
57.5°	414.9
60°	352.4
62.5°	289.8
65°	233.8
67.5°	181.1
70°	135.1
72.5°	92.2
75°	56.0
77.5°	26.3
80°	6.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)