

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857088

Luminaire Tested: **LX4C15D010 EX4C159030 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857088
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159030 4LBMH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1346.8 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857088

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857088

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106637
5°	107044
10°	107371
15°	107371
20°	106800
25°	104295
30°	97485
35°	84407
40°	65946
45°	47327
50°	30733
55°	18377
60°	10762
65°	6919
70°	4598
75°	3465
80°	2618
85°	0



TEST NUMBER: P857088

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.7	6.1
10°-20°	238.2	17.7
20°-30°	351.5	26.1
30°-40°	346.9	25.8
40°-50°	212.3	15.8
50°-60°	81.4	6.0
60°-70°	25.4	1.9
70°-80°	7.5	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	672.4	49.9
0°-40°	1019.2	75.7
0°-60°	1312.9	97.5
0°-90°	1346.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1346.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	868	
5°	868	83
15°	844	238
25°	769	352
35°	563	347
45°	272	212
55°	86	81
65°	24	25
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P857088

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	868.0
2.5°	869.9
5°	868.0
7.5°	866.3
10°	860.7
12.5°	853.4
15°	844.2
17.5°	833.3
20°	816.9
22.5°	798.7
25°	769.4
27.5°	732.8
30°	687.2
32.5°	630.5
35°	562.8
37.5°	487.9
40°	411.2
42.5°	339.9
45°	272.4
47.5°	211.9
50°	160.8
52.5°	118.8
55°	85.8
57.5°	60.3
60°	43.8
62.5°	32.9
65°	23.8
67.5°	18.3
70°	12.8
72.5°	9.2
75°	7.3
77.5°	3.7
80°	3.7
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)