

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857095

Luminaire Tested: **LX4C15D010 EX4C159030 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C15D010 EX4C159030 4LBWH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1497.6 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857095

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857095

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118578
5°	119031
10°	119397
15°	119403
20°	118749
25°	115966
30°	108394
35°	93855
40°	73323
45°	52609
50°	34192
55°	20455
60°	11966
65°	7674
70°	5137
75°	3845
80°	2901
85°	0



TEST NUMBER: P857095

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.9	6.1
10°-20°	264.9	17.7
20°-30°	390.8	26.1
30°-40°	385.7	25.8
40°-50°	236.0	15.8
50°-60°	90.5	6.0
60°-70°	28.3	1.9
70°-80°	8.3	0.6
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	747.6	49.9
0°-40°	1133.3	75.7
0°-60°	1459.8	97.5
0°-90°	1497.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1497.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	965	
5°	965	92
15°	939	265
25°	856	391
35°	626	386
45°	303	236
55°	96	90
65°	26	28
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P857095

CATALOG NUMBER: LX4C15D010 EX4C159030 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	965.2
2.5°	967.3
5°	965.2
7.5°	963.3
10°	957.1
12.5°	949.0
15°	938.8
17.5°	926.6
20°	908.3
22.5°	888.1
25°	855.5
27.5°	814.8
30°	764.1
32.5°	701.1
35°	625.8
37.5°	542.5
40°	457.2
42.5°	377.9
45°	302.8
47.5°	235.7
50°	178.9
52.5°	132.1
55°	95.5
57.5°	67.0
60°	48.7
62.5°	36.7
65°	26.4
67.5°	20.3
70°	14.3
72.5°	10.2
75°	8.1
77.5°	4.1
80°	4.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)