

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857621

Luminaire Tested: **LX4C30D010 EX4C309827 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P857621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309827 4LBNI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1854.9 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857621

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P857621

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	586404
5°	527710
10°	409088
15°	296105
20°	205023
25°	149462
30°	108607
35°	64265
40°	27023
45°	8426
50°	1089
55°	621
60°	713
65°	843
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857621

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.2	20.3
10°-20°	644.0	34.7
20°-30°	511.8	27.6
30°-40°	271.0	14.6
40°-50°	46.6	2.5
50°-60°	3.5	0.2
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1532.0	82.6
0°-40°	1802.9	97.2
0°-60°	1853.1	99.9
0°-90°	1854.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1854.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4773	
5°	4279	376
15°	2328	644
25°	1103	512
35°	428	271
45°	48	47
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857621

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4773.2
2.5°	4650.3
5°	4279.1
7.5°	3793.5
10°	3279.3
12.5°	2782.3
15°	2328.1
17.5°	1905.3
20°	1568.2
22.5°	1311.1
25°	1102.6
27.5°	934.1
30°	765.6
32.5°	594.2
35°	428.5
37.5°	282.9
40°	168.5
42.5°	97.1
45°	48.5
47.5°	17.1
50°	5.7
52.5°	5.7
55°	2.9
57.5°	2.9
60°	2.9
62.5°	2.9
65°	2.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)