

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857625

Luminaire Tested: **LX4C30D010 EX4C309827 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309827 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2106.3 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857625

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857625

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166798
5°	167435
10°	167937
15°	167938
20°	167018
25°	163112
30°	152442
35°	132009
40°	103120
45°	73996
50°	48068
55°	28766
60°	16855
65°	10814
70°	7220
75°	5411
80°	4033
85°	0



TEST NUMBER: P857625

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	6.1
10°-20°	372.5	17.7
20°-30°	549.7	26.1
30°-40°	542.5	25.8
40°-50°	332.0	15.8
50°-60°	127.3	6.0
60°-70°	39.8	1.9
70°-80°	11.7	0.6
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1051.6	49.9
0°-40°	1594.0	75.7
0°-60°	2053.3	97.5
0°-90°	2106.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2106.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1358	
5°	1358	129
15°	1320	373
25°	1203	550
35°	880	542
45°	426	332
55°	134	127
65°	37	40
75°	11	12
85°	0	2
90°	0	



TEST NUMBER: P857625

CATALOG NUMBER: LX4C30D010 EX4C309827 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1357.7
2.5°	1360.5
5°	1357.7
7.5°	1354.7
10°	1346.2
12.5°	1334.8
15°	1320.4
17.5°	1303.3
20°	1277.5
22.5°	1249.1
25°	1203.3
27.5°	1146.1
30°	1074.6
32.5°	986.1
35°	880.2
37.5°	763.1
40°	643.0
42.5°	531.6
45°	425.9
47.5°	331.5
50°	251.5
52.5°	185.8
55°	134.3
57.5°	94.3
60°	68.6
62.5°	51.5
65°	37.2
67.5°	28.6
70°	20.1
72.5°	14.3
75°	11.4
77.5°	5.7
80°	5.7
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)