

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857633

Luminaire Tested: **LX4C30D010 EX4C309830 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309830 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1637.2 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857633

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857633

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252538
5°	246917
10°	228303
15°	204861
20°	180327
25°	155196
30°	124978
35°	83207
40°	43269
45°	19581
50°	8505
55°	5719
60°	3661
65°	2587
70°	2155
75°	1377
80°	0
85°	0



TEST NUMBER: P857633

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.5	11.3
10°-20°	449.9	27.5
20°-30°	522.3	31.9
30°-40°	345.9	21.1
40°-50°	97.0	5.9
50°-60°	24.4	1.5
60°-70°	9.2	0.6
70°-80°	3.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.6	70.7
0°-40°	1503.5	91.8
0°-60°	1624.9	99.3
0°-90°	1637.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1637.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2056	
5°	2002	185
15°	1611	450
25°	1145	522
35°	555	346
45°	113	97
55°	27	24
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P857633

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2055.6
2.5°	2046.7
5°	2002.2
7.5°	1925.0
10°	1830.1
12.5°	1723.3
15°	1610.7
17.5°	1500.9
20°	1379.3
22.5°	1266.5
25°	1144.9
27.5°	1029.3
30°	881.0
32.5°	723.7
35°	554.8
37.5°	397.5
40°	269.8
42.5°	175.0
45°	112.7
47.5°	68.3
50°	44.5
52.5°	32.5
55°	26.7
57.5°	20.8
60°	14.9
62.5°	11.9
65°	8.9
67.5°	6.0
70°	6.0
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)