

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857559

Luminaire Tested: **LX4C30D010 EX4C309035 4LBNH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857559  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C30D010 EX4C309035 4LBNH  
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1862.0 lumens  
Efficiency: N/A  
Efficacy: 58.9 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857559

CATALOG NUMBER: LX4C30D010 EX4C309035 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P857559

CATALOG NUMBER: LX4C30D010 EX4C309035 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 94  | 98  | 95  | 92  |  | 95  | 93  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  |  | 90  | 86  | 84  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 73  | 81  | 76  | 73  |  | 80  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  |  | 67  | 63  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 74  | 65  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 62  | 57  | 53  | 71  | 62  | 56  | 53  | 61  | 56  | 53  |  | 60  | 56  | 52  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 287207 |
| 5°  | 280818 |
| 10° | 259639 |
| 15° | 232982 |
| 20° | 205089 |
| 25° | 176505 |
| 30° | 142129 |
| 35° | 94620  |
| 40° | 49219  |
| 45° | 22274  |
| 50° | 9671   |
| 55° | 6490   |
| 60° | 4152   |
| 65° | 2936   |
| 70° | 2443   |
| 75° | 1614   |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P857559

CATALOG NUMBER: LX4C30D010 EX4C309035 4LBNH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 210.9  | 11.3      |
| 10°-20°   | 511.6  | 27.5      |
| 20°-30°   | 594.0  | 31.9      |
| 30°-40°   | 393.4  | 21.1      |
| 40°-50°   | 110.3  | 5.9       |
| 50°-60°   | 27.7   | 1.5       |
| 60°-70°   | 10.4   | 0.6       |
| 70°-80°   | 3.6    | 0.2       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1316.6 | 70.7      |
| 0°-40°    | 1710.0 | 91.8      |
| 0°-60°    | 1848.1 | 99.2      |
| 0°-90°    | 1862.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1862.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2338 |      |
| 5°  | 2277 | 211  |
| 15° | 1832 | 512  |
| 25° | 1302 | 594  |
| 35° | 631  | 393  |
| 45° | 128  | 110  |
| 55° | 30   | 28   |
| 65° | 10   | 10   |
| 75° | 3    | 4    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P857559

CATALOG NUMBER: LX4C30D010 EX4C309035 4LBNH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2337.8 |
| 2.5°  | 2327.7 |
| 5°    | 2277.1 |
| 7.5°  | 2189.3 |
| 10°   | 2081.3 |
| 12.5° | 1959.9 |
| 15°   | 1831.8 |
| 17.5° | 1706.9 |
| 20°   | 1568.7 |
| 22.5° | 1440.5 |
| 25°   | 1302.1 |
| 27.5° | 1170.6 |
| 30°   | 1001.9 |
| 32.5° | 823.1  |
| 35°   | 630.9  |
| 37.5° | 452.1  |
| 40°   | 306.9  |
| 42.5° | 199.0  |
| 45°   | 128.2  |
| 47.5° | 77.7   |
| 50°   | 50.6   |
| 52.5° | 37.1   |
| 55°   | 30.3   |
| 57.5° | 23.7   |
| 60°   | 16.9   |
| 62.5° | 13.5   |
| 65°   | 10.1   |
| 67.5° | 6.8    |
| 70°   | 6.8    |
| 72.5° | 3.4    |
| 75°   | 3.4    |
| 77.5° | 3.4    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)