

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857573

Luminaire Tested: **LD4C30D010 EU4309040 4LBMLI**

Issue Date: 7/19/2024



Test Information

Test Method: LM-79-08
Report Number: P857573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30D010 EU4309040 4LBMLI
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2799.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857573

CATALOG NUMBER: LD4C30D010 EU4309040 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857573

CATALOG NUMBER: LD4C30D010 EU4309040 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542079
5°	532878
10°	489626
15°	410039
20°	328505
25°	263950
30°	196489
35°	112242
40°	52683
45°	22360
50°	7129
55°	3620
60°	2506
65°	1977
70°	1221
75°	0
80°	0
85°	0



TEST NUMBER: P857573

CATALOG NUMBER: LD4C30D010 EU4309040 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	399.5	14.3
10°-20°	893.2	31.9
20°-30°	888.0	31.7
30°-40°	483.6	17.3
40°-50°	111.8	4.0
50°-60°	15.7	0.6
60°-70°	5.9	0.2
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2180.7	77.9
0°-40°	2664.3	95.2
0°-60°	2791.8	99.7
0°-90°	2799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2799.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4412	
5°	4321	400
15°	3224	893
25°	1947	888
35°	748	484
45°	129	112
55°	17	16
65°	7	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P857573

CATALOG NUMBER: LD4C30D010 EU4309040 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4412.4
2.5°	4402.3
5°	4321.0
7.5°	4155.1
10°	3924.9
12.5°	3586.2
15°	3223.9
17.5°	2864.9
20°	2512.7
22.5°	2224.9
25°	1947.2
27.5°	1683.1
30°	1385.1
32.5°	1053.2
35°	748.4
37.5°	504.5
40°	328.5
42.5°	206.5
45°	128.7
47.5°	74.5
50°	37.3
52.5°	20.3
55°	16.9
57.5°	10.2
60°	10.2
62.5°	6.8
65°	6.8
67.5°	3.4
70°	3.4
72.5°	3.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)