

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857668

Luminaire Tested: **LX4C30D010 EX4C309850 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309850 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1930.6 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857668

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857668

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285733
5°	281879
10°	268659
15°	248600
20°	223797
25°	185912
30°	135149
35°	87601
40°	53020
45°	27329
50°	12366
55°	7454
60°	4988
65°	3576
70°	2694
75°	1756
80°	1132
85°	705



TEST NUMBER: P857668

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.0	11.1
10°-20°	545.4	28.3
20°-30°	616.8	31.9
30°-40°	372.7	19.3
40°-50°	130.6	6.8
50°-60°	33.4	1.7
60°-70°	12.8	0.7
70°-80°	4.3	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1376.2	71.3
0°-40°	1748.9	90.6
0°-60°	1912.9	99.1
0°-90°	1930.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2326	
5°	2286	214
15°	1955	545
25°	1372	617
35°	584	373
45°	157	131
55°	35	33
65°	12	13
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P857668

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2325.8
2.5°	2316.2
5°	2285.7
7.5°	2231.7
10°	2153.6
12.5°	2059.5
15°	1954.6
17.5°	1839.6
20°	1711.8
22.5°	1555.0
25°	1371.5
27.5°	1161.3
30°	952.7
32.5°	753.2
35°	584.1
37.5°	442.9
40°	330.6
42.5°	237.5
45°	157.3
47.5°	96.8
50°	64.7
52.5°	46.5
55°	34.8
57.5°	26.8
60°	20.3
62.5°	16.1
65°	12.3
67.5°	9.6
70°	7.5
72.5°	5.4
75°	3.7
77.5°	2.7
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)