

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857578

Luminaire Tested: **LX4C30D010 EX4C309040 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309040 4LBMH
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2244.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857578

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857578

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	93	90		95	91	88			91	88	86			89
3	99	91	85	80	97	90	84	80		87	82	78			84	80	77			82
4	92	83	77	72	90	82	76	71		80	75	70			78	73	70			76
5	87	77	70	65	85	76	69	64		74	68	64			72	67	63			70
6	81	71	64	58	80	70	63	58		68	62	58			67	61	57			65
7	76	65	58	53	75	65	58	53		63	57	53			62	56	52			61
8	72	60	53	49	70	60	53	49		59	53	48			58	52	48			57
9	68	56	49	45	66	56	49	45		55	49	44			54	48	44			53
10	64	52	46	41	63	52	46	41		51	45	41			50	45	41			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177695
5°	178374
10°	178915
15°	178927
20°	177934
25°	173766
30°	162414
35°	140648
40°	109872
45°	78826
50°	51203
55°	30650
60°	17937
65°	11512
70°	7651
75°	5791
80°	4316
85°	0



TEST NUMBER: P857578

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.7	6.1
10°-20°	396.9	17.7
20°-30°	585.7	26.1
30°-40°	578.0	25.8
40°-50°	353.7	15.8
50°-60°	135.6	6.0
60°-70°	42.4	1.9
70°-80°	12.4	0.6
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1120.3	49.9
0°-40°	1698.2	75.7
0°-60°	2187.5	97.5
0°-90°	2244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2244.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1446	
5°	1446	138
15°	1407	397
25°	1282	586
35°	938	578
45°	454	354
55°	143	136
65°	40	42
75°	12	12
85°	0	2
90°	0	



TEST NUMBER: P857578

CATALOG NUMBER: LX4C30D010 EX4C309040 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1446.4
2.5°	1449.4
5°	1446.4
7.5°	1443.3
10°	1434.2
12.5°	1422.0
15°	1406.8
17.5°	1388.5
20°	1361.0
22.5°	1330.7
25°	1281.9
27.5°	1221.0
30°	1144.9
32.5°	1050.6
35°	937.8
37.5°	813.0
40°	685.1
42.5°	566.4
45°	453.7
47.5°	353.1
50°	267.9
52.5°	198.0
55°	143.1
57.5°	100.4
60°	73.0
62.5°	54.9
65°	39.6
67.5°	30.5
70°	21.3
72.5°	15.2
75°	12.2
77.5°	6.1
80°	6.1
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)