

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857670

Luminaire Tested: **LX4C30D010 EX4C309850 4LBMH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857670  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C30D010 EX4C309850 4LBMH  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2042.0 lumens  
Efficiency: N/A  
Efficacy: 64.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857670

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P857670

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	161700
5°	162317
10°	162822
15°	162825
20°	161919
25°	158137
30°	147803
35°	127990
40°	99977
45°	71738
50°	46597
55°	27887
60°	16315
65°	10465
70°	6968
75°	5269
80°	3891
85°	0



TEST NUMBER: P857670

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.3	6.1
10°-20°	361.2	17.7
20°-30°	533.0	26.1
30°-40°	525.9	25.8
40°-50°	321.9	15.8
50°-60°	123.4	6.0
60°-70°	38.5	1.9
70°-80°	11.3	0.6
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1019.5	49.9
0°-40°	1545.4	75.7
0°-60°	1990.6	97.5
0°-90°	2042.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2042.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1316	
5°	1316	125
15°	1280	361
25°	1167	533
35°	853	526
45°	413	322
55°	130	123
65°	36	39
75°	11	11
85°	0	2
90°	0	



TEST NUMBER: P857670

CATALOG NUMBER: LX4C30D010 EX4C309850 4LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1316.2
2.5°	1319.1
5°	1316.2
7.5°	1313.4
10°	1305.2
12.5°	1294.1
15°	1280.2
17.5°	1263.5
20°	1238.5
22.5°	1211.0
25°	1166.6
27.5°	1111.1
30°	1041.9
32.5°	956.0
35°	853.4
37.5°	739.8
40°	623.4
42.5°	515.4
45°	412.9
47.5°	321.4
50°	243.8
52.5°	180.1
55°	130.2
57.5°	91.4
60°	66.4
62.5°	49.9
65°	36.0
67.5°	27.7
70°	19.4
72.5°	13.9
75°	11.1
77.5°	5.5
80°	5.5
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)