

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857697

Luminaire Tested: **LX4C30D010 EX4C309030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P857697
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309030 4LBMLI
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2579.3 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857697

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857697

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	815403
5°	733783
10°	568842
15°	411718
20°	285087
25°	207831
30°	151009
35°	89371
40°	37592
45°	11710
50°	1510
55°	878
60°	1007
65°	1192
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857697

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	523.1	20.3
10°-20°	895.5	34.7
20°-30°	711.7	27.6
30°-40°	376.8	14.6
40°-50°	64.9	2.5
50°-60°	4.9	0.2
60°-70°	2.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2130.2	82.6
0°-40°	2507.0	97.2
0°-60°	2576.8	99.9
0°-90°	2579.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2579.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6637	
5°	5950	523
15°	3237	895
25°	1533	712
35°	596	377
45°	67	65
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857697

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6637.2
2.5°	6466.3
5°	5950.1
7.5°	5274.9
10°	4559.9
12.5°	3868.8
15°	3237.1
17.5°	2649.3
20°	2180.6
22.5°	1823.1
25°	1533.2
27.5°	1298.9
30°	1064.5
32.5°	826.2
35°	595.9
37.5°	393.4
40°	234.4
42.5°	135.1
45°	67.4
47.5°	23.9
50°	7.9
52.5°	7.9
55°	4.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)