

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857629

Luminaire Tested: **LX4C30D010 EX4C309830 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309830 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1862.9 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857629

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857629

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275708
5°	271988
10°	259228
15°	239862
20°	215940
25°	179392
30°	130397
35°	84542
40°	51159
45°	26374
50°	11926
55°	7175
60°	4816
65°	3459
70°	2586
75°	1756
80°	1061
85°	705



TEST NUMBER: P857629

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.5	11.1
10°-20°	526.3	28.3
20°-30°	595.1	31.9
30°-40°	359.7	19.3
40°-50°	126.0	6.8
50°-60°	32.2	1.7
60°-70°	12.4	0.7
70°-80°	4.2	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1327.9	71.3
0°-40°	1687.5	90.6
0°-60°	1845.8	99.1
0°-90°	1862.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1862.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2244	
5°	2206	206
15°	1886	526
25°	1323	595
35°	564	360
45°	152	126
55°	34	32
65°	12	12
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P857629

CATALOG NUMBER: LX4C30D010 EX4C309830 4LBMDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2244.2
2.5°	2234.9
5°	2205.5
7.5°	2153.4
10°	2078.0
12.5°	1987.2
15°	1885.9
17.5°	1775.0
20°	1651.7
22.5°	1500.4
25°	1323.4
27.5°	1120.6
30°	919.2
32.5°	726.8
35°	563.7
37.5°	427.3
40°	319.0
42.5°	229.2
45°	151.8
47.5°	93.5
50°	62.4
52.5°	44.9
55°	33.5
57.5°	25.8
60°	19.6
62.5°	15.5
65°	11.9
67.5°	9.3
70°	7.2
72.5°	5.2
75°	3.7
77.5°	2.6
80°	1.5
82.5°	1.1
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)