

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857682

Luminaire Tested: **LX4C30D010 EX4C309030 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857682
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C30D010 EX4C309030 4LBMDLI
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2232.9 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857682

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P857682

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		66
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360292
5°	372558
10°	376342
15°	339005
20°	281727
25°	221034
30°	161748
35°	83582
40°	39709
45°	13969
50°	3154
55°	2056
60°	1450
65°	1105
70°	754
75°	522
80°	424
85°	0



TEST NUMBER: P857682

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.5	12.9
10°-20°	734.2	32.9
20°-30°	742.9	33.3
30°-40°	378.7	17.0
40°-50°	74.2	3.3
50°-60°	9.0	0.4
60°-70°	3.8	0.2
70°-80°	1.4	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1765.6	79.1
0°-40°	2144.3	96.0
0°-60°	2227.6	99.8
0°-90°	2232.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2232.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2933	
5°	3021	289
15°	2665	734
25°	1631	743
35°	557	379
45°	80	74
55°	10	9
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P857682

CATALOG NUMBER: LX4C30D010 EX4C309030 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2932.7
2.5°	2959.8
5°	3021.0
7.5°	3056.1
10°	3016.8
12.5°	2884.2
15°	2665.4
17.5°	2407.3
20°	2154.9
22.5°	1893.5
25°	1630.6
27.5°	1368.7
30°	1140.2
32.5°	859.2
35°	557.3
37.5°	373.2
40°	247.6
42.5°	155.5
45°	80.4
47.5°	28.7
50°	16.5
52.5°	12.2
55°	9.6
57.5°	7.5
60°	5.9
62.5°	4.8
65°	3.8
67.5°	2.7
70°	2.1
72.5°	1.6
75°	1.1
77.5°	1.1
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)