

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857764

Luminaire Tested: **LX4C35D010 EX4C359035 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P857764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359035 4LBSLI
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3602.0 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857764

CATALOG NUMBER: LX4C35D010 EX4C359035 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P857764

CATALOG NUMBER: LX4C35D010 EX4C359035 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102		109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88		102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77		95	87	81	77		84	79	75		82	78	74		79	76	73
4	90	81	73	68		88	79	73	68		77	71	67		75	70	66		73	69	65
5	84	73	66	61		82	72	65	60		70	64	60		69	63	59		67	62	59
6	79	67	60	54		77	66	59	54		65	58	54		63	58	53		62	57	53
7	74	62	54	49		72	61	54	49		60	53	49		58	53	48		57	52	48
8	69	57	50	45		68	57	50	45		55	49	45		54	49	44		53	48	44
9	65	53	46	41		64	53	46	41		52	45	41		51	45	41		50	44	41
10	61	50	43	38		60	49	42	38		48	42	38		47	42	38		46	41	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315979
5°	308813
10°	290003
15°	269802
20°	250232
25°	228110
30°	203085
35°	180002
40°	161785
45°	144796
50°	124213
55°	99919
60°	74449
65°	47529
70°	22917
75°	3797
80°	2830
85°	0



TEST NUMBER: P857764

CATALOG NUMBER: LX4C35D010 EX4C359035 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.2	6.5
10°-20°	594.8	16.5
20°-30°	770.7	21.4
30°-40°	755.2	21.0
40°-50°	640.1	17.8
50°-60°	419.6	11.6
60°-70°	168.6	4.7
70°-80°	19.3	0.5
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1598.7	44.4
0°-40°	2353.9	65.3
0°-60°	3413.5	94.8
0°-90°	3602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3602.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2572	
5°	2504	233
15°	2121	595
25°	1683	771
35°	1200	755
45°	833	640
55°	466	420
65°	164	169
75°	8	19
85°	0	1
90°	0	



TEST NUMBER: P857764

CATALOG NUMBER: LX4C35D010 EX4C359035 4LBSLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2572.0
2.5°	2552.0
5°	2504.1
7.5°	2424.4
10°	2324.7
12.5°	2217.0
15°	2121.3
17.5°	2017.7
20°	1914.0
22.5°	1802.4
25°	1682.8
27.5°	1559.1
30°	1431.6
32.5°	1311.9
35°	1200.2
37.5°	1108.6
40°	1008.8
42.5°	921.1
45°	833.4
47.5°	741.7
50°	649.9
52.5°	558.3
55°	466.5
57.5°	382.8
60°	303.0
62.5°	231.2
65°	163.5
67.5°	107.7
70°	63.8
72.5°	27.9
75°	8.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)