

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857715

Luminaire Tested: **LX4C35D010 EX4C359027 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359027 4LBMDH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2371.0 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857715

CATALOG NUMBER: LX4C35D010 EX4C359027 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857715

CATALOG NUMBER: LX4C35D010 EX4C359027 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350919
5°	346179
10°	329935
15°	305300
20°	274837
25°	228327
30°	165975
35°	107593
40°	65112
45°	33549
50°	15195
55°	9146
60°	6143
65°	4390
70°	3305
75°	2183
80°	1415
85°	987



TEST NUMBER: P857715

CATALOG NUMBER: LX4C35D010 EX4C359027 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.8	11.1
10°-20°	669.8	28.3
20°-30°	757.4	31.9
30°-40°	457.8	19.3
40°-50°	160.3	6.8
50°-60°	41.0	1.7
60°-70°	15.7	0.7
70°-80°	5.3	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1690.1	71.3
0°-40°	2147.8	90.6
0°-60°	2349.2	99.1
0°-90°	2371.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2371.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2856	
5°	2807	263
15°	2400	670
25°	1684	757
35°	717	458
45°	193	160
55°	43	41
65°	15	16
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P857715

CATALOG NUMBER: LX4C35D010 EX4C359027 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2856.4
2.5°	2844.5
5°	2807.1
7.5°	2740.7
10°	2644.8
12.5°	2529.2
15°	2400.4
17.5°	2259.2
20°	2102.2
22.5°	1909.7
25°	1684.4
27.5°	1426.2
30°	1170.0
32.5°	925.0
35°	717.4
37.5°	543.9
40°	406.0
42.5°	291.7
45°	193.1
47.5°	118.9
50°	79.5
52.5°	57.2
55°	42.7
57.5°	32.8
60°	25.0
62.5°	19.7
65°	15.1
67.5°	11.8
70°	9.2
72.5°	6.6
75°	4.6
77.5°	3.3
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)