

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857781

Luminaire Tested: **LX4C35D010 EX4C359040 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P857781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359040 4LBMLI
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3304.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857781

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857781

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1044574
5°	940003
10°	728707
15°	527433
20°	365203
25°	266241
30°	193453
35°	114477
40°	48144
45°	15011
50°	1949
55°	1092
60°	1253
65°	1483
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857781

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	670.1	20.3
10°-20°	1147.1	34.7
20°-30°	911.7	27.6
30°-40°	482.6	14.6
40°-50°	83.1	2.5
50°-60°	6.2	0.2
60°-70°	3.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2728.9	82.6
0°-40°	3211.5	97.2
0°-60°	3300.9	99.9
0°-90°	3304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8503	
5°	7622	670
15°	4147	1147
25°	1964	912
35°	763	483
45°	86	83
55°	5	6
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857781

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	8502.6
2.5°	8283.7
5°	7622.3
7.5°	6757.4
10°	5841.4
12.5°	4956.1
15°	4146.9
17.5°	3393.9
20°	2793.4
22.5°	2335.5
25°	1964.1
27.5°	1663.9
30°	1363.7
32.5°	1058.4
35°	763.3
37.5°	503.8
40°	300.2
42.5°	173.0
45°	86.4
47.5°	30.6
50°	10.2
52.5°	10.2
55°	5.1
57.5°	5.1
60°	5.1
62.5°	5.1
65°	5.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)