

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857784

Luminaire Tested: **LX4C35D010 EX4C359040 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P857784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359040 4LBSH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3459.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857784

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P857784

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		93	92	90
2	102	96	90	85		100	94	88	84		90	86	82		87	83	80		84	81	79
3	95	85	78	73		92	84	77	72		81	75	71		78	74	70		76	72	69
4	87	77	69	63		85	75	68	63		73	67	62		71	65	61		69	64	60
5	81	69	61	55		79	68	61	55		66	60	55		64	59	54		63	58	53
6	75	63	55	49		73	62	54	49		60	54	49		59	53	48		57	52	48
7	70	58	50	44		68	57	49	44		55	49	44		54	48	43		53	47	43
8	65	53	45	40		64	52	45	40		51	44	39		50	44	39		49	43	39
9	61	49	41	36		60	48	41	36		47	40	36		46	40	36		45	40	35
10	58	45	38	33		56	45	38	33		44	37	33		43	37	33		42	37	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222242
5°	221216
10°	216651
15°	208778
20°	199166
25°	188433
30°	177749
35°	167359
40°	157583
45°	146898
50°	133941
55°	118296
60°	100126
65°	78604
70°	56107
75°	30759
80°	5448
85°	0



TEST NUMBER: P857784

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.4	4.9
10°-20°	460.6	13.3
20°-30°	639.6	18.5
30°-40°	698.0	20.2
40°-50°	651.1	18.8
50°-60°	494.2	14.3
60°-70°	270.6	7.8
70°-80°	74.5	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1269.6	36.7
0°-40°	1967.6	56.9
0°-60°	3112.9	90.0
0°-90°	3459.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3459.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1809	
5°	1794	169
15°	1642	461
25°	1390	640
35°	1116	698
45°	846	651
55°	552	494
65°	270	271
75°	65	74
85°	0	1
90°	0	



TEST NUMBER: P857784

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1809.0
2.5°	1809.0
5°	1793.8
7.5°	1771.0
10°	1736.7
12.5°	1691.0
15°	1641.5
17.5°	1580.6
20°	1523.4
22.5°	1454.8
25°	1390.1
27.5°	1325.4
30°	1253.0
32.5°	1184.4
35°	1115.9
37.5°	1047.3
40°	982.6
42.5°	914.0
45°	845.5
47.5°	776.9
50°	700.8
52.5°	628.4
55°	552.3
57.5°	479.8
60°	407.5
62.5°	335.2
65°	270.4
67.5°	209.4
70°	156.2
72.5°	106.7
75°	64.8
77.5°	30.4
80°	7.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)