

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857737

Luminaire Tested: **LX4C35D010 EX4C359030 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359030 4LBMDLI
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2865.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857737

CATALOG NUMBER: LX4C35D010 EX4C359030 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P857737

CATALOG NUMBER: LX4C35D010 EX4C359030 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		66
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	462298
5°	478048
10°	482890
15°	434993
20°	361490
25°	283606
30°	207554
35°	107263
40°	50935
45°	17913
50°	4052
55°	2635
60°	1843
65°	1395
70°	970
75°	665
80°	495
85°	0



TEST NUMBER: P857737

CATALOG NUMBER: LX4C35D010 EX4C359030 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	370.2	12.9
10°-20°	942.0	32.9
20°-30°	953.2	33.3
30°-40°	485.9	17.0
40°-50°	95.3	3.3
50°-60°	11.5	0.4
60°-70°	4.8	0.2
70°-80°	1.7	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2265.5	79.1
0°-40°	2751.4	96.0
0°-60°	2858.2	99.8
0°-90°	2865.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2865.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3763	
5°	3876	370
15°	3420	942
25°	2092	953
35°	715	486
45°	103	95
55°	12	12
65°	5	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P857737

CATALOG NUMBER: LX4C35D010 EX4C359030 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3763.0
2.5°	3797.8
5°	3876.4
7.5°	3921.4
10°	3870.9
12.5°	3700.8
15°	3420.1
17.5°	3088.8
20°	2765.0
22.5°	2429.6
25°	2092.2
27.5°	1756.1
30°	1463.1
32.5°	1102.5
35°	715.2
37.5°	478.8
40°	317.6
42.5°	199.5
45°	103.1
47.5°	36.9
50°	21.2
52.5°	15.7
55°	12.3
57.5°	9.6
60°	7.5
62.5°	6.1
65°	4.8
67.5°	3.4
70°	2.7
72.5°	2.0
75°	1.4
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)