

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857835

Luminaire Tested: **LX4C35D010 EX4C359830 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359830 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1932.3 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857835

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857835

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298079
5°	291436
10°	269470
15°	241783
20°	212854
25°	183174
30°	147505
35°	98190
40°	51079
45°	23108
50°	10034
55°	6747
60°	4324
65°	3052
70°	2514
75°	1661
80°	0
85°	0



TEST NUMBER: P857835

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.9	11.3
10°-20°	531.0	27.5
20°-30°	616.5	31.9
30°-40°	408.2	21.1
40°-50°	114.5	5.9
50°-60°	28.8	1.5
60°-70°	10.8	0.6
70°-80°	3.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1366.4	70.7
0°-40°	1774.6	91.8
0°-60°	1917.9	99.3
0°-90°	1932.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1932.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2426	
5°	2363	219
15°	1901	531
25°	1351	616
35°	655	408
45°	133	114
55°	32	29
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P857835

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBNH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2426.3
2.5°	2415.7
5°	2363.2
7.5°	2272.1
10°	2160.1
12.5°	2034.0
15°	1901.0
17.5°	1771.4
20°	1628.1
22.5°	1494.9
25°	1351.3
27.5°	1214.8
30°	1039.8
32.5°	854.2
35°	654.7
37.5°	469.1
40°	318.5
42.5°	206.5
45°	133.0
47.5°	80.6
50°	52.5
52.5°	38.4
55°	31.5
57.5°	24.6
60°	17.6
62.5°	14.0
65°	10.5
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)