

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857840

Luminaire Tested: **LX4C35D010 EX4C359830 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359830 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2584.3 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857840

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857840

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204637
5°	205419
10°	206047
15°	206056
20°	204919
25°	200132
30°	187041
35°	161975
40°	126535
45°	90797
50°	58962
55°	35298
60°	20664
65°	13285
70°	8836
75°	6645
80°	4952
85°	0



TEST NUMBER: P857840

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.6	6.1
10°-20°	457.1	17.7
20°-30°	674.5	26.1
30°-40°	665.6	25.8
40°-50°	407.3	15.8
50°-60°	156.1	6.0
60°-70°	48.9	1.9
70°-80°	14.3	0.6
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1290.2	49.9
0°-40°	1955.7	75.7
0°-60°	2519.2	97.5
0°-90°	2584.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2584.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1666	
5°	1666	159
15°	1620	457
25°	1476	674
35°	1080	666
45°	523	407
55°	165	156
65°	46	49
75°	14	14
85°	0	2
90°	0	



TEST NUMBER: P857840

CATALOG NUMBER: LX4C35D010 EX4C359830 4LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1665.7
2.5°	1669.3
5°	1665.7
7.5°	1662.2
10°	1651.7
12.5°	1637.6
15°	1620.1
17.5°	1599.0
20°	1567.4
22.5°	1532.5
25°	1476.4
27.5°	1406.1
30°	1318.5
32.5°	1209.9
35°	1080.0
37.5°	936.2
40°	789.0
42.5°	652.2
45°	522.6
47.5°	406.7
50°	308.5
52.5°	228.0
55°	164.8
57.5°	115.7
60°	84.1
62.5°	63.2
65°	45.7
67.5°	35.1
70°	24.6
72.5°	17.6
75°	14.0
77.5°	7.0
80°	7.0
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)