

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857850

Luminaire Tested: **LX4C35D010 EX4C359835 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P857850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359835 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3080.1 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857850

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P857850

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197892
5°	196983
10°	192924
15°	185910
20°	177346
25°	167789
30°	158272
35°	149032
40°	140311
45°	130792
50°	119263
55°	105338
60°	89142
65°	70000
70°	49965
75°	27388
80°	4811
85°	0



TEST NUMBER: P857850

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.9	4.9
10°-20°	410.1	13.3
20°-30°	569.5	18.5
30°-40°	621.5	20.2
40°-50°	579.8	18.8
50°-60°	440.1	14.3
60°-70°	241.0	7.8
70°-80°	66.3	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1130.5	36.7
0°-40°	1752.1	56.9
0°-60°	2771.9	90.0
0°-90°	3080.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3080.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1611	
5°	1597	151
15°	1462	410
25°	1238	570
35°	994	622
45°	753	580
55°	492	440
65°	241	241
75°	58	66
85°	0	1
90°	0	



TEST NUMBER: P857850

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1610.8
2.5°	1610.8
5°	1597.3
7.5°	1577.0
10°	1546.5
12.5°	1505.8
15°	1461.7
17.5°	1407.4
20°	1356.5
22.5°	1295.4
25°	1237.8
27.5°	1180.2
30°	1115.7
32.5°	1054.7
35°	993.7
37.5°	932.6
40°	874.9
42.5°	813.9
45°	752.8
47.5°	691.8
50°	624.0
52.5°	559.6
55°	491.8
57.5°	427.3
60°	362.8
62.5°	298.5
65°	240.8
67.5°	186.5
70°	139.1
72.5°	95.0
75°	57.7
77.5°	27.1
80°	6.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)