

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857787

Luminaire Tested: **LX4C35D010 EX4C359040 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359040 4LBWH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2943.0 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857787

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857787

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	233041
5°	233931
10°	234640
15°	234661
20°	233367
25°	227907
30°	213015
35°	184456
40°	144096
45°	103393
50°	67162
55°	40203
60°	23539
65°	15116
70°	10058
75°	7595
80°	5660
85°	0



TEST NUMBER: P857787

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.6	6.1
10°-20°	520.5	17.7
20°-30°	768.1	26.1
30°-40°	758.0	25.8
40°-50°	463.9	15.8
50°-60°	177.8	6.0
60°-70°	55.6	1.9
70°-80°	16.3	0.6
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1469.3	49.9
0°-40°	2227.2	75.7
0°-60°	2868.9	97.5
0°-90°	2943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2943.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1897	
5°	1897	181
15°	1845	521
25°	1681	768
35°	1230	758
45°	595	464
55°	188	178
65°	52	56
75°	16	16
85°	0	2
90°	0	



TEST NUMBER: P857787

CATALOG NUMBER: LX4C35D010 EX4C359040 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1896.9
2.5°	1900.9
5°	1896.9
7.5°	1892.9
10°	1880.9
12.5°	1865.0
15°	1845.0
17.5°	1821.0
20°	1785.0
22.5°	1745.2
25°	1681.3
27.5°	1601.3
30°	1501.6
32.5°	1377.8
35°	1229.9
37.5°	1066.2
40°	898.5
42.5°	742.8
45°	595.1
47.5°	463.2
50°	351.4
52.5°	259.6
55°	187.7
57.5°	131.7
60°	95.8
62.5°	72.0
65°	52.0
67.5°	40.0
70°	28.0
72.5°	20.0
75°	16.0
77.5°	8.0
80°	8.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)