

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857799

Luminaire Tested: **LX4C35D010 EX4C359050 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359050 4LBMDH
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2555.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857799

CATALOG NUMBER: LX4C35D010 EX4C359050 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857799

CATALOG NUMBER: LX4C35D010 EX4C359050 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	378143
5°	373039
10°	355546
15°	328995
20°	296161
25°	246044
30°	178856
35°	115932
40°	70164
45°	36156
50°	16380
55°	9853
60°	6610
65°	4738
70°	3556
75°	2373
80°	1486
85°	987



TEST NUMBER: P857799

CATALOG NUMBER: LX4C35D010 EX4C359050 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.2	11.1
10°-20°	721.8	28.3
20°-30°	816.2	31.9
30°-40°	493.3	19.3
40°-50°	172.8	6.8
50°-60°	44.2	1.7
60°-70°	16.9	0.7
70°-80°	5.7	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1821.2	71.3
0°-40°	2314.5	90.6
0°-60°	2531.5	99.1
0°-90°	2555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3078	
5°	3025	283
15°	2587	722
25°	1815	816
35°	773	493
45°	208	173
55°	46	44
65°	16	17
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P857799

CATALOG NUMBER: LX4C35D010 EX4C359050 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3078.0
2.5°	3065.3
5°	3024.9
7.5°	2953.4
10°	2850.1
12.5°	2725.5
15°	2586.7
17.5°	2434.5
20°	2265.3
22.5°	2057.9
25°	1815.1
27.5°	1536.9
30°	1260.8
32.5°	996.7
35°	773.0
37.5°	586.2
40°	437.5
42.5°	314.3
45°	208.1
47.5°	128.1
50°	85.7
52.5°	61.6
55°	46.0
57.5°	35.4
60°	26.9
62.5°	21.2
65°	16.3
67.5°	12.7
70°	9.9
72.5°	7.1
75°	5.0
77.5°	3.5
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)