

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857827

Luminaire Tested: **LX4C35D010 EX4C359827 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359827 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2486.3 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857827

CATALOG NUMBER: LX4C35D010 EX4C359827 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857827

CATALOG NUMBER: LX4C35D010 EX4C359827 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	67	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196873
5°	197625
10°	198226
15°	198234
20°	197140
25°	192527
30°	179948
35°	155825
40°	121740
45°	87340
50°	56745
55°	33970
60°	19878
65°	12762
70°	8477
75°	6408
80°	4811
85°	0



TEST NUMBER: P857827

CATALOG NUMBER: LX4C35D010 EX4C359827 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.6	6.1
10°-20°	439.7	17.7
20°-30°	648.9	26.1
30°-40°	640.3	25.8
40°-50°	391.9	15.8
50°-60°	150.3	6.0
60°-70°	47.0	1.9
70°-80°	13.8	0.6
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.2	49.9
0°-40°	1881.5	75.7
0°-60°	2423.7	97.5
0°-90°	2486.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2486.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1602	
5°	1602	153
15°	1559	440
25°	1420	649
35°	1039	640
45°	503	392
55°	159	150
65°	44	47
75°	14	14
85°	0	2
90°	0	



TEST NUMBER: P857827

CATALOG NUMBER: LX4C35D010 EX4C359827 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1602.5
2.5°	1605.8
5°	1602.5
7.5°	1599.1
10°	1589.0
12.5°	1575.4
15°	1558.6
17.5°	1538.3
20°	1507.9
22.5°	1474.3
25°	1420.3
27.5°	1352.8
30°	1268.5
32.5°	1164.0
35°	1039.0
37.5°	900.7
40°	759.1
42.5°	627.5
45°	502.7
47.5°	391.3
50°	296.9
52.5°	219.4
55°	158.6
57.5°	111.3
60°	80.9
62.5°	60.8
65°	43.9
67.5°	33.8
70°	23.6
72.5°	16.9
75°	13.5
77.5°	6.8
80°	6.8
82.5°	3.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)