

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857916

Luminaire Tested: **LX4C40D010 EX4C409030 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409030 4LBNH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2515.0 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857916

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P857916

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387934
5°	379304
10°	350706
15°	314687
20°	277008
25°	238398
30°	191978
35°	127795
40°	66475
45°	30092
50°	13054
55°	8760
60°	5602
65°	3983
70°	3269
75°	2183
80°	0
85°	0



TEST NUMBER: P857916

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.9	11.3
10°-20°	691.1	27.5
20°-30°	802.3	31.9
30°-40°	531.3	21.1
40°-50°	149.0	5.9
50°-60°	37.4	1.5
60°-70°	14.1	0.6
70°-80°	4.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1778.3	70.7
0°-40°	2309.6	91.8
0°-60°	2496.1	99.2
0°-90°	2515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2515.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3158	
5°	3076	285
15°	2474	691
25°	1759	802
35°	852	531
45°	173	149
55°	41	37
65°	14	14
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P857916

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3157.7
2.5°	3144.0
5°	3075.7
7.5°	2957.1
10°	2811.3
12.5°	2647.2
15°	2474.2
17.5°	2305.5
20°	2118.8
22.5°	1945.6
25°	1758.7
27.5°	1581.1
30°	1353.3
32.5°	1111.8
35°	852.1
37.5°	610.6
40°	414.5
42.5°	268.7
45°	173.2
47.5°	104.9
50°	68.3
52.5°	50.1
55°	40.9
57.5°	32.0
60°	22.8
62.5°	18.3
65°	13.7
67.5°	9.1
70°	9.1
72.5°	4.6
75°	4.6
77.5°	4.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)