

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857845

Luminaire Tested: **LX4C35D010 EX4C359835 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359835 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2590.5 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857845

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P857845

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		66
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417997
5°	432246
10°	436620
15°	393314
20°	326858
25°	256427
30°	187665
35°	96975
40°	46059
45°	16210
50°	3670
55°	2377
60°	1671
65°	1250
70°	898
75°	570
80°	424
85°	0



TEST NUMBER: P857845

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.8	12.9
10°-20°	851.8	32.9
20°-30°	861.9	33.3
30°-40°	439.4	17.0
40°-50°	86.1	3.3
50°-60°	10.4	0.4
60°-70°	4.3	0.2
70°-80°	1.5	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2048.4	79.1
0°-40°	2487.8	96.0
0°-60°	2584.4	99.8
0°-90°	2590.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2590.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3402	
5°	3505	335
15°	3092	852
25°	1892	862
35°	647	439
45°	93	86
55°	11	10
65°	4	4
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P857845

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3402.4
2.5°	3433.9
5°	3505.0
7.5°	3545.7
10°	3500.0
12.5°	3346.3
15°	3092.4
17.5°	2792.8
20°	2500.1
22.5°	2196.9
25°	1891.7
27.5°	1587.9
30°	1322.9
32.5°	996.8
35°	646.6
37.5°	432.9
40°	287.2
42.5°	180.3
45°	93.3
47.5°	33.4
50°	19.2
52.5°	14.2
55°	11.1
57.5°	8.6
60°	6.8
62.5°	5.5
65°	4.3
67.5°	3.1
70°	2.5
72.5°	1.9
75°	1.2
77.5°	1.2
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)