

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857846

Luminaire Tested: **LX4C35D010 EX4C359835 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C35D010 EX4C359835 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2357.8 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857846

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P857846

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186700
5°	187414
10°	187996
15°	187996
20°	186968
25°	182591
30°	170656
35°	147787
40°	115437
45°	82822
50°	53802
55°	32193
60°	18846
65°	12093
70°	8046
75°	6076
80°	4528
85°	0



TEST NUMBER: P857846

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.7	6.1
10°-20°	417.0	17.7
20°-30°	615.4	26.1
30°-40°	607.3	25.8
40°-50°	371.6	15.8
50°-60°	142.4	6.0
60°-70°	44.5	1.9
70°-80°	13.1	0.6
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1177.1	49.9
0°-40°	1784.4	75.7
0°-60°	2298.4	97.5
0°-90°	2357.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2357.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1520	
5°	1520	145
15°	1478	417
25°	1347	615
35°	985	607
45°	477	372
55°	150	142
65°	42	45
75°	13	13
85°	0	2
90°	0	



TEST NUMBER: P857846

CATALOG NUMBER: LX4C35D010 EX4C359835 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1519.7
2.5°	1522.9
5°	1519.7
7.5°	1516.5
10°	1507.0
12.5°	1494.1
15°	1478.1
17.5°	1458.9
20°	1430.1
22.5°	1398.2
25°	1347.0
27.5°	1282.9
30°	1203.0
32.5°	1103.8
35°	985.4
37.5°	854.2
40°	719.8
42.5°	595.1
45°	476.7
47.5°	371.1
50°	281.5
52.5°	208.0
55°	150.3
57.5°	105.5
60°	76.7
62.5°	57.6
65°	41.6
67.5°	32.0
70°	22.4
72.5°	16.1
75°	12.8
77.5°	6.4
80°	6.4
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)