

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857896

Luminaire Tested: **LX4C40D010 EX4C409027 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P857896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409027 4LBNLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2850.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857896

CATALOG NUMBER: LX4C40D010 EX4C409027 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P857896

CATALOG NUMBER: LX4C40D010 EX4C409027 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	901044
5°	810847
10°	628584
15°	454962
20°	315026
25°	229655
30°	166869
35°	98744
40°	41537
45°	12944
50°	1682
55°	942
60°	1081
65°	1279
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857896

CATALOG NUMBER: LX4C40D010 EX4C409027 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	578.0	20.3
10°-20°	989.5	34.7
20°-30°	786.4	27.6
30°-40°	416.3	14.6
40°-50°	71.7	2.5
50°-60°	5.4	0.2
60°-70°	2.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2353.9	82.6
0°-40°	2770.2	97.2
0°-60°	2847.3	99.9
0°-90°	2850.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2850.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7334	
5°	6575	578
15°	3577	990
25°	1694	786
35°	658	416
45°	74	72
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857896

CATALOG NUMBER: LX4C40D010 EX4C409027 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7334.3
2.5°	7145.4
5°	6575.0
7.5°	5828.8
10°	5038.8
12.5°	4275.1
15°	3577.1
17.5°	2927.5
20°	2409.6
22.5°	2014.6
25°	1694.2
27.5°	1435.3
30°	1176.3
32.5°	913.0
35°	658.4
37.5°	434.6
40°	259.0
42.5°	149.3
45°	74.5
47.5°	26.4
50°	8.8
52.5°	8.8
55°	4.4
57.5°	4.4
60°	4.4
62.5°	4.4
65°	4.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)